

## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 100A 2" NPT Hub, Angled, Mounting Screws Included Aluminium moulé

Par Hubbell Wiring Device-Kellems  
No de catalogue [BB1002W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessory, Back Box, For 100A 2" NPT Hub, Angled, Mounting Screws Included, Gray Cast Aluminum.



### Performance

Environmental - Moisture Resistance - IP67 Suitability

### Général

Numéro de catalogue	BB1002W
Couleur	
La construction	Casting
Indicateur RoHS de l'UE	Non
Type d'article	Boîte de montage
Les Knockouts	2" NPT Hub
Matériau	Aluminium
Matériau - Matériel de montage	Vis de montage
Nombre de prises	Accepte 1 appareil
Série	Boîtes d'encastrement et adaptateurs
Style	15 Degré
Plage de température	Limité par l'appareil
Type	Boîte à dos angulaire
CUP	783585390857

### Dimensions

Taille de l'affichage	Pour les appareils de 100 et 125 ampères
-----------------------	--

### Chef d'orchestre

Entrée par câble	Par le biais du Hub
------------------	---------------------

### Certifications et conformité

Norme(s) industrielle(s)	Test d'étanchéité à la pluie et de givrage externe UL
--------------------------	---

### Logistique

Quantité de cartons	1
Quantité de palettes	195

### Documentation

[Catalogues - WDK Catalog Full 2024](#)  
[Dessins de vente - WDK\\_BB1002W\\_DRAWING\\_PDF](#)  
[Garantie - Industrial & Commercial Products](#)  
[Littérature - Dual-Certified IEC Pin & Sleeve Devices](#)  
[Littérature - Hubbell Marine Full Line Catalog](#)  
[Littérature - IEC Pin & Sleeve Devices](#)  
[Littérature - Hubbell PRO Pin & Sleeve Brochure](#)  
[Page du catalogue - WDK G-11 Catalog Page](#)  
[Page du catalogue - WDK AA-21 Catalog Page](#)  
[Page du catalogue - WDK G-35 Catalog Page](#)  
[Page du catalogue - WDK AA-20 Catalog Page](#)  
[Page du catalogue - WDK G-12 Catalog Page](#)  
[Page du catalogue - WDK G-28 Catalog Page](#)  
[Spécifications - BB1002W](#)  
[Spécifications - Wiring BB1002W Specification Sheet](#)

