




Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 250V, 6-15P, Yellow, Single Pack



By Hubbell Wiring Device-Kellems
Catalog # [HBL5666VY](#)

Valise® Straight Blade Male Plug15A, 2-Pole, 3-Wire Grounding, 250V, 6-15P/White.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Horsepower - Maximum	1.5
Item Type	Valise Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB or better • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #18-#12 AWG stranded copper wire only • Mechanical - Terminal

Dimensions

Dimensions	1.88 in x 1.5 in x 1.13 in
Height	1.13 in
Length	1.88 in
Weight	0.15 lb
Width	1.5 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	6-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-40 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1237_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL5666VY_DRAWING_PDF](#)

• Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498 and CSA

Series	Valise®
Style	Standard
Type	<ul style="list-style-type: none">• Plug• Plugs
UPC	783585013053



A proud member of the Hubbell Family.