

HUBBELL
Wiring Device-Kellems

GFHW13105

By Hubbell Wiring Device-Kellems
Catalog # [GFHW13105](#)

Power Protection Products, Hard Wired GFCI,
Industrial/Commercial, No Output, 30A 120V AC, 4-6 mA Trip
Level, Yellow.



Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Mécanisme de loquet électromagnétique
- Se déclenche si la terre et le neutre se touchent du côté de la charge
- Voyant rouge clignotant et alarme sonore en option
- Protection contre l'ouverture du neutre Se déclenche en cas de perte du neutre

General

Application	
Catalog Number	GFHW13105
Color	
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Thermoplastic
Performance	Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure Electrical - Operating Voltage Range - 85% to 110% Electrical - Rated Voltage - 120V AC, 240V AC & 120/240V, 3Ø 250V AC, 3Ø 120/208V AC Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency Environmental - Construction - Industrial grade design Environmental - Housing Rating - UL Type 4X Environmental - Leakage Current - At 93% Humidity leakage current is zero Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F. Environmental - Type - Class A GFCI
Series	Extra Heavy Duty
Style	Automatic Set
Temperature Rating	De -35 degrés C à 66 degrés C (de -30 degrés F à 150 degrés F)
Type	
UPC	783585005232

Dimensions

Weight	1.55 lb
--------	---------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Hard Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK K-18 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFHW13105 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1827_INSTALLINST](#)
[Literature - 20A & 30A GFCI Protected Cord Drops](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Safety Product Guide](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_GFHW13_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-GFW13105-SPEC-EN | REV 6/2024