



Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 2-Wire Non-Grounding, 15A 125V, 1-15P, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5866VY](#)



Valise® Polarized Straight Blade Male Plug 15A, 2-Pole 2-Wire Non-Grounding, 125V, 1-15P.

Features

- Hinged one piece body design for easy assembly
- Two captive multiple drive assembly screws
- Powerful cord grips prevent conductor slippage and strain
- Polarized blades

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Horsepower - Maximum	0.5
Item Type	Valise Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Molded Rating on Device Face • Mechanical - Terminal Accommodation - #18-#14 AWG stranded copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance

Dimensions

Dimensions	1.68 in x 1.25 in x 0.88 in
Height	0.88 in
Length	1.68 in
Weight	0.1 lb
Width	1.25 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	2-Wire
Wire Size	#18 AWG to #14 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	1-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-41 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD2442_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL5866VY_DRAWING_PDF](#)

Series	Valise®
Style	Non-Grounding
Type	<ul style="list-style-type: none">• Plug• Plugs
UPC	783585013077



A proud member of the Hubbell Family.