

HUBBELL
Wiring Device-Kellems

GFP4305

By Hubbell Wiring Device-Kellems
Catalog # [GFP4305](#)

Power Protection Products, GFCI High Amperage Portables,
Industrial/Commercial, Manual Set, 30A 3-Phase 120/208V AC, 6'
Cord Length, 4-6 mA Trip Level, Black.



Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Mécanisme de verrouillage électromagnétique
- Déclenchement en cas de contact de terre et neutre au côté de la charge
- Lumière clignotante rouge et alarme sonore facultative
- Protection neutre ouverte
- Déclenche en cas de perte de neutre

General

Application	Line Cord Only No Devices
Catalog Number	GFP4305
Color	
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
Performance	Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure Electrical - Operating Voltage Range - 85% to 110% Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency Environmental - Construction - Industrial grade design Environmental - Housing Rating - UL Type 4X Environmental - Leakage Current - At 93% Humidity leakage current is zero Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F. Environmental - Type - Meets UL943 Class A GFCI
Series	Extra Heavy Duty
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Straight Blade
UPC	783585521367

Dimensions

Outside Diameter	0.335
------------------	-------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase 120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	5
Strands	Multi

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M9094_ACAD](#)
[Engineering Drawing - GFP4305 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1978_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - M9094](#)
[Sales Drawings - WDK_GFP4305_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-GFP4305-SPEC-EN | REV 6/2024