

Power Protection Devices,  
Receptacle, Self Test, GFCI, WR,  
Commercial Grade, 15A 125V, 2-Pole  
3-Wire Grounding, 5-15R, Light  
Almond

By Hubbell Wiring Device-Kellems  
Catalog # [GFRWR15LA](#)

Power Protection Devices, Receptacle, Self Test, GFCI, WR,  
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,  
Light Almond

Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

|                   |                                                                                                                                                                                                                                                     |
|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number    | GFRWR15LA                                                                                                                                                                                                                                           |
| Color             | Light Almond                                                                                                                                                                                                                                        |
| EU RoHS Indicator | Contact Manufacturer                                                                                                                                                                                                                                |
| Series            | Heavy Duty                                                                                                                                                                                                                                          |
| Specifications    | <ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Zinc plated steel</li><li>• Power Contacts - Brass</li></ul> |
| Style             | Standard                                                                                                                                                                                                                                            |
| Type              | Weather Resistant                                                                                                                                                                                                                                   |
| UPC               | 883778999741                                                                                                                                                                                                                                        |

Electrical Ratings

|                            |       |
|----------------------------|-------|
| Current / Amperage Rating  | 15 A  |
| Voltage Rating Description | 125 V |

Certifications And Compliance

|                      |                             |
|----------------------|-----------------------------|
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating          | 5-15R                       |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - WDK K-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFRWR15LA AutoCAD Drawing](#)
- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Installation Manuals - PD2987](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Sell Sheets - Commercial GFCI- French](#)
- [Sell Sheets - Commercial GFCI- English](#)
- [Specifications - GFRWR15LA Specification Sheet English](#)
- [Specifications - WIRING\\_GFRWR15LA\\_spec](#)
- [Specifications - GFRWR15LA](#)

