



Wiring Device-Kellems

GFTWRST82SNAPR

By Hubbell Wiring Device-Kellems
Catalog # [GFTWRST82SNAPR](#)

Straight Blade SNAP-Connect Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R.



Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Hospital Grade

General

Color	<ul style="list-style-type: none"> • Red • Rouge
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Weather Resistant
Horsepower - Maximum	0.5
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Style	Standard
Type	<ul style="list-style-type: none"> • Tamper-Resistant, Weather Resistant • Tamper-Resistant, Weather Resistant
UPC	783585486444

Dimensions

Dimensions	3.28 in x 1.77 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.77 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Wire Size	#12 AWG
-----------	---------

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-5 Catalog Page](#)
- [Catalog Page - WDK L-14 Catalog Page](#)
- [Catalog Page - WDK A-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - GFTWRST82SNAPR AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2484_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Sales Drawings - WDK_GFTWRST82SNAP_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - SNAPConnect Devices](#)
- [Video - Tamper-Resistant Receptacles](#)

Related Products

[SNAPIRA](#)





A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-GFTWRST82SNAPR-SPEC-EN | REV 1/2024