

# CONN, WATERTIGHT, 5-20R, 20A, 125V, CLEAR, WIRING CONDITION

By Hubbell Wiring Device-Kellems  
Catalog # [HBL15W33AWC](#)



CONN, WATERTIGHT, 5-20R, 20A, 125V, CLEAR, WIRING CONDITION

## Features

- Power indicating LED also confirms wiring condition of the device
- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection

## Performance

- Electrical: Current Interrupting- Rated for current interruption per UL498
- Electrical: Dielectric Voltage- 2500V AC
- Electrical: Max Working Voltage- As marked
- Electrical: Temperature Rise- 30°C max per UL498 at rated current
- Mechanical: Cord Accomodation- 0.375"-0.625" (9.5-15.9)
- Environmental: Moisture Resistance- UL Listed 4, 4X, 12, 6, 6P
- Environmental: Operating Temperature- -40°C (without impact) to +60°C continuous
- Environmental: UV resistance- All exposed materials are UV stabilized

## General

Catalog Number	HBL15W33AWC
Color	Clear
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2 Pole
Series	Watertight
Specifications	<ul style="list-style-type: none"><li>• Body: Thermoplastic Elastomer</li><li>• Contact Carrier: White Nylon</li><li>• Terminal Retainer: Clear polycarbonate</li><li>• Contacts: Nickel plated brass</li><li>• Core: White Nylon</li><li>• Bushing &amp; Cone Seal: Black Elastomer</li></ul>

- Gotcha Ring: Nylon
- Strain Relief Nut: PBT
- Terminal Screws: Nickel plated brass

Type	Connector
UPC	783585580630

## Electrical Ratings

Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3 Wire
-----------------	--------

## Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
----------------------	--

## Logistics

Carton Quantity	25
Pallet Quantity	1375

## Product Assets

- [Catalog Page - WDK C-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2854\\_INSTALLINST](#)
- [Literature - Watertight Wiring Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - M-12620](#)
- [Specifications - HBL15W33AWC Specification Sheet French](#)
- [Specifications - Wiring HBL15W33AWC Specification Sheet](#)
- [Specifications - HBL15W33AWC Specification Sheet English](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Hubbell Watertight Devices](#)