

EdgeConnect™ Twist-Lock® Receptacle with Spring Termination, 20A, 250V, L6, 20R, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL2320ST](#)

20A, 250V EdgeConnect™ Twist-Lock® Receptacle with Spring Termination



Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

General

Application	
Catalog Number	HBL2320ST
Color	
Environmental Conditions	
Insulation	N/A
Item Type	Single Receptacle
Material	Nylon
Mounting Type	
Number Of Poles	2
Size	Standard Sized Product
Temperature Rating	Maximum continu 75°C ; Minimum -40°C (sans impact)
UPC	783585569550

Dimensions

Dimensions	3.28 in x 1.70 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V Minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3
Wire Size	14 AWG - 10 AWG solid, 14 AWG - 8 AWG stranded (including compact stranded)

Certifications And Compliance

Industry Standard(s)	UL Listed To UL 498 CSA Certified to Specification C22.2 No. 42
Nema Rating	L6-20R

Logistics

Carton Quantity	30
Pallet Quantity	3060

Product Assets

[3D Product View - Twist-Lock® EdgeConnect HBL2320ST](#)
[Receptacle AR Model](#)
[Brochures - EdgeConnect Brochure](#)
[Brochures - Twist-Lock Edge Series French](#)
[Brochures - Twist-Lock Edge Series](#)
[Brochures - EdgeConnect Brochure French](#)
[Catalog Page - WDK B-35 Catalog Page](#)
[Catalog Page - WDK B-27 Catalog Page](#)
[Catalog Page - WDK B-23 Catalog Page](#)
[Catalog Page - WDK B-33 Catalog Page](#)
[Catalog Page - WDK B-31 Catalog Page](#)
[Catalog Page - WDK B-21 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M13891_ACAD](#)
[Installation Manuals - PD2880](#)
[Literature - Healthcare Product Solutions](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - Twist-Lock® Edge Series Devices](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - M13891](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Twist-Lock® Edge Plugs and Inlets](#)
[Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)
[Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL2320ST-SPEC-EN | REV 6/2024