

Kellems Wire Management, Cord
Connectors, Junior, SNAP-IN,
.30-.36", Black

By Hubbell Wiring Device-Kellems
Catalog # [HS1003BPK25](#)

Kellems Wire Management, Cord Connectors, Junior, SNAP-IN,
.30-.36", Black

Features

- Miniature nylon snap-in cord connector with spiral
- Available in gray or black

Application

Straight Snap-In Connector

Performance

- Environmental - Flammability - Hubbell Juniors have a UL 94V-2 rating
- Environmental - Operating Temperature - -40°F to +225°F (-40°C to +107°C)

General

Catalog Number	HS1003BPK25
EU RoHS Indicator	Yes
Environmental Conditions	Non-Weather Resistant
Item Type	Juniors® Miniature Snap-In Cord Connectors with Spiral
Material	Nylon
Material - Mounting Hardware	Snap-In
Series	Miniature
Specifications	• Cord Diameter Range Inches (mm) - .30"- .36" (7.6-9.1) • For Chassis Thickness - .13" (3.2) Max • Material - Nylon • Packaging - Bulk packed 25 per carton
Temperature Rating	Minimum -40°F to +225°F (-40°C to +107°C)
Type	Snap-In Connector
UPC	783585023397



Dimensions

Display Size .63" Actual (16.0)

Conductor Related

Conductor Range 0.30-0.36 in (7.6-9.1 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - WDK W-76 Catalog Page](#)
[Catalog Page - WDK W-77 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1702_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Specifications - HS1003BPK25 Specification Sheet French](#)
[Specifications - Wiring HS1003BPK25 Specification Sheet](#)
[Specifications - HS1003BPK25 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)