

# EdgeConnect™ Twist-Lock® Receptacle with Spring Termination, 20A, 277/480V, L22, 20R, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2520ST](#)

EdgeConnect™ Twist-Lock® Receptacle, 20A 277/480V, L22-20R, BK, with Spring Termination.



## Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

## General

Catalog Number	HBL2520ST
Item Type	20A, 3 phase wye, 277/480 V AC Twist-Lock Receptacle with Spring Termination
Number Of Poles	4
UPC	783585788517

## Dimensions

Dimensions	3.28 in x 1.7 in x 1.468 in
Height	1.468 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	20 A
Voltage Rating	277/480 VAC

## Conductor Related

Number Of Wires	5
Wire Size	14 AWG - 10 AWG solid, 14 AWG - 8 AWG stranded (including compact stranded)

## Logistics

Carton Quantity 30

## Product Assets

- [3D Product View - Twist-Lock® EdgeConnect HBL2320ST Receptacle AR Model](#)
- [Brochures - EdgeConnect Brochure](#)
- [Brochures - Twist-Lock Edge Series French](#)
- [Brochures - Twist-Lock Edge Series](#)
- [Brochures - EdgeConnect Brochure French](#)
- [Catalog Page - WDK B-35 Catalog Page](#)
- [Catalog Page - WDK B-27 Catalog Page](#)
- [Catalog Page - WDK B-23 Catalog Page](#)
- [Catalog Page - WDK B-33 Catalog Page](#)
- [Catalog Page - WDK B-31 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14072\\_ACAD](#)
- [Installation Manuals - PD2880](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - M14072](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock® Edge Plugs and Inlets](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)
- [Video](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-HBL2520ST-SPEC-EN | REV 6/2024