



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 600V AC

By Hubbell Wiring Device-Kellems
 Catalog # [HBL460MIF5W](#)



Heavy Duty IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, Terminal.

Features

- Replaceable spring-loaded receptacle liftcover with gasket
- Removable door for ease of wiring and installation
- Plug-Check™ mechanism to detect the presence of plug

Application

High Ampacity Connections

General

Color	<ul style="list-style-type: none"> • Black • Noir
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage • Electrical - Dielectric Voltage - Withstands 3,000V AC Min • Electrical - Max Working Voltage - 600V AC • Environmental - Flammability - UL94-5VA and V-0 Classification • Environmental - Ingress Protection - IP66 Suitability • Environmental - Operating Temperatures - Max. Continuous +75°C • Min. Continuous -40°C • Environmental - UV Resistance - All materials are UV stabilized • Mechanical - Impact Resistance - In accordance

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC
Wattage	36000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed for US and Canada
Nema Rating	Non-NEMA

Product Assets

- [Catalog Page - WDK G-27 Catalog Page](#)
- [Catalog Page - WDK G-26 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL460MIF5W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1781_INSTALLINST](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
- [Sales Drawings - WDK_HBL460MIF_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

with UL 746C

- Mechanical - Mounting - External adjustment feet
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series

Fused

Style

Standard Service

Type

- Mechanical Interlock
- Mechanical Interlock

UPC

783585406015



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL460MIF5W-SPEC-EN | REV 1/2024