



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Delta 480V AC, Watertight- Reversed Service

By Hubbell Wiring Device-Kellems
Catalog # [HBL460P7WR](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, Terminal Screws, Red, Watertight- Reversed Service.

Features

- Gasketed sealing ring provides watertight seal
- Heavy duty external cord grips

General

Color	<ul style="list-style-type: none"> • Red • Rouge
Environmental Conditions	Watertight
Item Type	Male Plug- Reversed
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 3,000V AC Min • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17 • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Watertight per IEC 60309-1 • Environmental - Operating Temperature - Maximum Continuous 75°C • Minimum - 40°C w/o impact • Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682 • Mechanical - Product Identification -

Dimensions

Display Size Standard Sized

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Standard C22.2 No. 182.1 • UL Classified to IEC60309-1 • UL Listed, File E146032
----------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating Non-NEMA

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK G-22 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL460P7WR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)
[Literature - IEC Pin & Sleeve Devices](#)
[Sales Drawings - WDK_HBL460P_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Identification and ratings are a permanent part of the device housing.

- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Series

Non-Fused

Style

Reverse Service

Type

- Watertight Mating Plug

- Mating Plug

UPC

783585012742



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL460P7WR-SPEC-EN | REV 1/2024