



Kellems Wire Management, Liquidtight System, SwivelLok® Multi-Position Male Liquid Tight Connector, 1", Non-Metallic, Black

By Hubbell Wiring Device-Kellems
Catalog # [PS1009NBK](#)



Polytuff® Non-Metallic Liquidtight SwivelLok® Multi Position 1"
Fitting.

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection
- Swiveled to any position from straight to 90°

Application

Fittings are to be used with Polytuff® I and Polytuff® II

General

Color	<ul style="list-style-type: none">• Black• Noir
Material	Nylon
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94X-2• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style Type	SwivelLok® Multi-Position <ul style="list-style-type: none">• Polytuff® SwivelLok® Non-Metallic Liquidtight Fittings• Polytuff® SwivelLok® Non-Metallic Liquidtight Fittings
UPC	783585339184

Dimensions

Trade Size	1
------------	---

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed:UL50 Type 4X, 12 and 13
----------------------	---

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK W-90 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - PS1009NBK AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1859_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Industrial Solutions](#)
[Sales Drawings - WDK_PS1009N_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)

Related Products

[G1100 - Kellems Wire Management, Liquidtight System, Non-Metallic Polytuff® I Conduit, Gray, 1", 100 feet](#)
[B2100 - Kellems Wire Management, Liquidtight System, Polytuff® II Non-Metallic Tubing, 1", 100 feet, Black](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-PS1009NBK-SPEC-EN | REV 1/2024