

Wallplates and Boxes, Box Covers,
1-Gang, 1) Duplex Opening, For
Portable Outlet Box, White

By Hubbell Wiring Device-Kellems
Catalog # [HBLP8FSL](#)

Wallplates and Boxes, Box Covers, 1-Gang, 1) Duplex Opening,
For Portable Outlet Box, White

Features

- Impact resistant Valox® cover plate

Application


1) Duplex Opening

Performance

- Environmental - Flammability - UL 94V-0, 94-5VA classification
- Environmental - Impact and Crush Resistance - In accordance with UL 514C, UL50, C22.2 No. 18 and C22.2 No. 94.
- Environmental - Moisture Resistance - Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates.Dry, indoors locations, Enclosure Type 1 with all other cover plates
- Environmental - Operating Temperature - 80°C maximum
- -35°C minimum
- Environmental - UV Resistance - All materials are UV stabilized

General

Catalog Number	HBLP8FSL
Color	White
Construction	Molded
Cord Range	.38" - .75"
EU RoHS Indicator	Yes
Item Type	Weatherproofing Covers
Knockouts	None
Material	Thermoplastic
Material - Mounting Hardware	Box Mount- Mounting Screws
Number Of Outlets	1-Device
Specifications	<ul style="list-style-type: none">• Bonding Strap - Brass• Cord Connector - Nylon nut• Nylon Gotcha® ring• Neoprene grommet• Gasket - UL recognized closed-cell foam



Style	Grounding Screw - Brass
Type	Indoor Screws - Zinc Plated Steel
UPC	Non-Metallic Fs Cover Plate Cover Plate 783585708591

Dimensions

Display Size	1-Gang
Length	4.56 in
Weight	0.05 lb
Width	2.84 in

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No. 0.4• UL 514C, UL467 and UL50 Enclosures Types 1, 3R
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - WDK C-12 Catalog Page](#)
[Catalog Page - WDK H-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Safety Product Guide](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBLP8FSL_DRAWING_PDF](#)
[Specifications - WIRING_HBLP8FSL_spec](#)
[Specifications - HBLP8FSL Specification Sheet French](#)
[Specifications - HBLP8FSL Specification Sheet English](#)
[Video - Watertight Products](#)
[Video - Watertight Products](#)