

## Recessed 10" Series, Kit

By Hubbell Wiring Device-Kellems  
Catalog # [S1R10PTBRZ](#)

Fire Rated Poke Throughs, Recessed 10" Series, Kit, Includes (1) S1R10PTFIT, (1) S1R10CVRBRZ, (2) S1R10PSPREPBRKT, (4) S1R10CBFPT, (3) S1R10PBFBLANK, (1) S1R10PBF075, (1) S1R10CENTERDIV, (1) S1R10PERIMDIV

### Features

- For use with a 10.00" to 10.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

### Application

10" Fire-Rated Poke-Through Series

### General

Accessory Type	10" FRPT Kit
Application - For Use On	Concrete
Catalog Number	S1R10PTBRZ
Construction	Fabricated
Construction Material - Main	10 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	Antique Bronze Plated Cover
Item Type	10" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	10" Core Hole
Size	Standard Sized Product
Style	FRPT Kits
Sub Brand	SystemOne Recessed
Type	10" Recessed Rated Poke Through Kit
UPC	783585548234



### Conductor Related

Cable Entry Through Cover

### Certifications And Compliance

Industry Standard(s) 

- cULus Listed
- Meets ADA Standards
- UL 514A Listed

### Product Assets

[BIM - Electrical\\_Equipment-Poke\\_Through-Hubbell\\_Wiring-System\\_One-S1R10](#)  
[Catalog Page - WDK P-7 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - 10 INCH RECESSED FRPT AutoCAD Drawing](#)  
[Engineering Drawing - S1R10PTBRZ AutoCAD Drawing](#)  
[Literature - Hubbell SystemOne 10 Inch Fire-Rated Poke-Throughs](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)  
[Sales Drawings - WDK\\_S1R10PT\\_DRAWING\\_PDF](#)  
[Specifications - S1R10PTBRZ Specification Sheet English](#)  
[Specifications - S1R10PTBRZ Specification Sheet French](#)  
[Specifications - Wiring S1R10PTBRZ Specification Sheet](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - SystemOne 10" FRPT](#)  
[Video - SystemOne 10" FRPT](#)