

SystemOne, Sub-Plate, Recessed
Bezel for (6) Ortronics TracJack
Modules, Single 20A, 125V
Receptacle, Black

By Hubbell Wiring Device-Kellems
Catalog # [S1SPTRAC](#)

In-Floor Delivery Systems, SystemOne, Sub-Plate, Recessed
Bezel for (6) Ortronics TracJack Modules, Single 20A, 125V
Receptacle, Black

Features

- Durable Cast Aluminum Construction
- Black Powder Coat Finish
- Large Capacity and Multi-Service Applications
- Open System Subplates for Maximum Data Flexibility

General

Catalog Number	S1SPTRAC
Construction	Cast Aluminum
Cover Shape	Round
EU RoHS Indicator	Contact Manufacturer
Finish Type	Black
Item Type	Flush Sub-Plate
Material	Composite
Mounting Method	To Fitting in Floor
Number Of Outlets	Recessed Bezel for (6) Ortronics TracJack Modules, Single 20A, 125V Receptacle
Specifications	• Order Quantity - Carton of 1 • Product Type - SystemOne Sub Plates • Sub-Plate Format - Ortronics® TracTack & Power • Subplates for - SystemOne Boxes and Poke-Throughs • Unit Package - Single
UPC	783585371252



Dimensions

Dimensions	5.36 in x 5.36 in x 6.26 in
Height	6.26 in
Length	5.36 in
Width	5.36 in

Certifications And Compliance

Industry Standard(s)	cULus
----------------------	-------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Brochures - Floorbox Selection Guide](#)
[Catalog Page - WDK O-22 Catalog Page](#)
[Catalog Page - WDK P-30 Catalog Page](#)
[Catalog Page - WDK P-29 Catalog Page](#)
[Catalog Page - WDK O-23 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - S1SPTRAC AutoCAD Drawing](#)
[Engineering Drawing - Legacy SystemOne Solution Drawing](#)
[Installation Manuals - WIRING_PD2286_INSTALLINST](#)
[Sales Drawings - WDK_S1_DRAWING_PDF](#)
[Sales Drawings - WDK_S1SPTRAC_DRAWING_PDF](#)
[Specifications - S1SPTRAC Specification Sheet French](#)
[Specifications - Wiring S1SPTRAC Specification Sheet](#)
[Specifications - S1SPTRAC Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)