

Kellems Wire Management, Cord
Connectors, Straight Male, 2.19-
2.31", 2 1/2", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [SHC1080](#)

Kellems Wire Management, Cord Connectors, Straight Male, 2.19-
2.31", 2 1/2", Aluminum

Features

- Cast aluminum cord connector, one-piece design with machined threads
- Lock nuts sold separately

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)

General

Catalog Number	SHC1080
EU RoHS Indicator	Yes
Item Type	Cord Connectors
Material	Aluminum, Cast
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	• Cord Diameter Range Inches (mm) - 2.19"-2.31" (55.6-58.7) • Material - Cast Aluminum • NPT Hub Size - 2 1/2 Inch
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)
UPC	783585200804

Dimensions

Display Size	2 1/2" NPT
--------------	------------



Hub Size	2-1/2"
----------	--------

Conductor Related

Conductor Range	2.19-2.31 in (55.6- 58.7 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK W-70 Catalog Page](#)
- [Catalog Page - WDK W-71 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - SHC1080 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1856_INSTALLINST](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Sales Drawings - WDK_SHC1080_DRAWINGS_PDF](#)
- [Specifications - SHC1080 Specification Sheet French](#)
- [Specifications - SHC1080 Specification Sheet](#)
- [Specifications - Wiring SHC1080 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)