

TradeSelect, Decorator Switch,  
Residential Grade, Rocker Switch,  
General Purpose AC, 4 Way, 15A  
120/277V AC, Push Back and Side  
Wired

By Hubbell Wiring Device-Kellems  
Catalog # [RSD415W](#)

tradeSELECT® Decorator Switch, Residential Grade, Rocker  
Switch, General Purpose AC, Four Way, 15A 120/277V AC, Push  
Back and Side Wired

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

|                   |                                                                                                                                                                                                                        |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number    | RSD415W                                                                                                                                                                                                                |
| EU RoHS Indicator | Yes                                                                                                                                                                                                                    |
| Specifications    | <ul style="list-style-type: none"><li>• Base and body - PVC</li><li>• Contacts - Copper alloy</li><li>• Mounting strap - Galvanized steel</li><li>• Rocker - Polycarbonate</li><li>• Terminal screws - Steel</li></ul> |



UPC  
883778101441

Certifications And Compliance

Industry Standard(s)  
• CSA Certified  
• UL Listed E3896

Logistics

Carton Quantity 10  
Pallet Quantity 4500

Product Assets

[Catalog Page - WDK Z-3 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD2444\\_INSTALLINST](#)  
[Literature - Residential Catalog](#)  
[Literature - Residential Product Guide](#)  
[Sales Drawings - WDK\\_RSD415\\_DRAWING\\_PDF](#)  
[Specifications - RSD415W Specification Sheet English](#)  
[Specifications - RSD415W Specification Sheet French](#)  
[Specifications - WIRING\\_RSD415W\\_spec](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)  
[Video - Tradeselect Devices](#)  
[Video - Tradeselect Devices](#)