

Spider II Portable Power, Complete Unit, Locking Style, With 6) 20A 125V Receptacles- 1) 60A 3-Phase Wye 120/208V AC, Inlet and Outlet

By Hubbell Wiring Device-Kellems
Catalog # [SCTLO](#)

Temporary Power Products, Spider II Portable Power, Complete Unit, Locking Style, With 6) 20A 125V Receptacles- 1) 60A 3-Phase Wye 120/208V AC , Inlet and Outlet, Yellow

Features

- Individual GFCI modules
- TYPE 3R metallic enclosure and heavy duty,abuse resistant legs
- Standard stab termination circuit breakers with gasketed lift cover

Application

Heavy Duty Portable

Performance

Environment - Moisture Resistance - Indoor and outdoor wet and dry locations

General

Catalog Number	SCTLO
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Twist-Lock® Singles
Material	Thermoplastic
Material - Mounting Hardware	Non-Mounted, Portable
Number Of Poles	4-Pole
Series	Spider II
Specifications	• Code Compliance - NEC®, ANSI/NFPA 70 • Enclosure Type - 3R, rainproof, suitable for use in damp locations
Type	6-20A, 125V Straight Blade Receptacles, 1-60A, 3 Phase Wye 120/208V AC, Inlet and Outlet, Yellow
UPC	783585940014



Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pre-Wired
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	• Three Phase 120 VAC • Three Phase 208 VAC
Voltage Rating Description	3-Phase 120/208 VAC
Wattage	12480

Conductor Related

Number Of Wires	5-Wire Grounding
-----------------	------------------

Certifications And Compliance

Industry Standard(s)	UL and cUL Listed
Nema Rating	6) L5-20R, 1) 60A Non-NEMA In/Out

Product Assets

[Catalog Page - WDK H-12 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1869_INSTALLINST](#)
[Literature - Safety Product Guide](#)
[Literature - Education Application Guide](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_SCTLO_DRAWING_PDF](#)
[Specifications - SCTLO Specification Sheet French](#)
[Specifications - SCTLO Specification Sheet](#)
[Specifications - Wiring SCTLO Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)