

# Locking Devices, Hubbellock, Industrial, Flush Receptacle, 30A 3- Phase Delta 480V AC, 3-Pole 4- Wire Grounding, Non-NEMA, Screw Terminal, Red

By Hubbell Wiring Device-Kellems  
Catalog # [HBL20443](#)

Locking Devices, Hubbellock®, Industrial, Flush Receptacle, 30A  
3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, Non-NEMA,  
Screw Terminal, Red.

## Application

Heavy Duty Industrial

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0 for Receptacles and Inlets.HB or better for Plugs and Connectors
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #10 AWG - #6 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL20443
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Grounding Hubbellock® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Bridge - Zinc plated steel</li><li>• Contacts - Bronze</li><li>• Device Color - Black/Red Shutter</li><li>• Housing - Thermoset</li><li>• Shutter - Thermoset</li></ul>



Type	Receptacle
UPC	783585017419
	• Terminal Screws - Zinc plated steel

## Dimensions

Dimensions	3.28 in x 1.94 in x 1.75 in
Display Size	Standard Sized Product
Height	1.75 in
Length	3.28 in
Weight	0.55 lb
Width	1.94 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

## Logistics

Carton Quantity	20
Pallet Quantity	3060

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL20443](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL20443-SPEC-EN | REV 10/2024