

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Safety Shroud, Surface Mount  
Receptacle, 20A 125V, 2-Pole 3-  
Wire Grounding, L5- 20R, Screw  
Terminal, Gray**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2310SR](#)

Locking Devices, Twist-Lock®, Safety-Shroud®, Surface Mount  
Receptacle, 20A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-  
20R, Screw Terminal, Gray



## General

Application	
Catalog Number	HBL2310SR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	20A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 Environmental - Moisture Resistance - IP20 Suitability Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only. Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Surface Mount Receptacle
	Surface Mount Receptacle
UPC	783585234021

## Dimensions

Dimensions	4.56 in x 2.84 in x 1.58 in
Display Size	Standard Sized Product
Height	1.58 in
Length	4.56 in
Weight	0.45 lb
Width	2.84 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Fed.Spec. W-C-596 Listed to UL 498
Nema Rating	L5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	1320

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2310SR-SPEC-EN | REV 6/2024