

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Industrial, Flush Receptacle, 20A  
250V AC, 2-Pole 3-Wire Grounding,  
L6-20R, Screw Terminal, Black**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2320](#)

Locking Devices, Twist-Lock®, Industrial, Single Flush  
Receptacle, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-  
20R, Screw Terminal, Nylon face, Back and side wired, Black.



## General

Application	
Catalog Number	HBL2320
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Receptacles
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17  Environmental - Moisture Resistance - IP20 Suitability  Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)  Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Single Flush Receptacle
	Single Flush Receptacle
UPC	783585235585

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.23 in
Display Size	Standard Sized Product
Height	1.23 in
Length	3.28 in
Weight	0.25 lb
Width	1.7 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42  Fed.Spec. W-C-596  Listed to UL 498
Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4050

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2320-SPEC-EN | REV 6/2024