

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Insulgrip® Connector, 20A 250V
AC, 2-Pole 3-Wire Grounding,
NEMA L6-20R, Black nylon.**

By Hubbell Wiring Device-Kellems
Catalog # [HBL2323BK](#)

Locking Devices, Twist-Lock®, Insulgrip® Connector, 20A 250V
AC, 2-Pole 3-Wire Grounding, NEMA L6-20R, Black nylon.



General

Application	
Catalog Number	HBL2323BK
Color	
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Insulation	Insulated Body
Item Type	20A Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact Electrical - Current Interrupting - Certified for current interrupting at full rated current
Performance	Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6 Environmental - Moisture Resistance - IP20 Suitability Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only. Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
UPC	783585172231

Dimensions

Dimensions	2.26 in x 2.26 in x 3.86 in
Display Size	Standard
Height	3.86 in
Length	2.26 in
Weight	0.5 lb
Width	2.26 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Fed.Spec. W-C-596 Listed to UL 498
Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	30
Pallet Quantity	2550

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2323BK-SPEC-EN | REV 6/2024