

HUBBELL
Wiring Device-Kellems

**Locking Devices, Hubbellock,
Industrial, Receptacle, 60A 600V 4-
Pole 5-Wire Grounding, Non NEMA,
Screw Terminal, Blue**

By Hubbell Wiring Device-Kellems
Catalog # [HBL26520](#)

Hubbellock® Industrial Receptacle, 60A 600V AC, 4-Pole 5-Wire
Grounding phenolic interior with longuminum housing and lift
cover, Non NEMA, Screw Terminal



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Moisture Resistance - IP44 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #8 AWG - #4 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26520
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Hubbell® Grounding Receptacle
Material	Aluminum
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Contacts / Springs - Copper alloy• Flange Gasket - Neoprene• Housing / Cover - Cast Aluminum• Mounting Screws - Zinc plated steel• Receptacle Interior - Phenolic• Rivet - Aluminum• Spring - Stainless steel• Terminal - Copper• Terminal Screws - Stainless steel

Type	Receptacle
UPC	783585017518

Dimensions

Dimensions	3.5 in x 4.62 in x 4.96 in
Display Size	Standard Sized Product
Height	4.96 in
Length	3.5 in
Weight	2.55 lb
Width	4.62 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA Standard• Listed to UL Standard
----------------------	---

Logistics

Carton Quantity	5
Pallet Quantity	560

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL26520](#)
[Warranty - Industrial & Commercial Products](#)