

# Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 250V DC/600 V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Phenolic, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3771](#)



Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 250V DC/600 V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Phenolic, Black

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

## General

Catalog Number	HBL3771
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Receptacle
Material	Phenolic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Body - Phenolic</li><li>• Contacts - Brass</li><li>• Face - Phenolic</li><li>• Insulator - Phenolic</li><li>• Terminal Screws - Steel</li></ul>
Type	Receptacle
UPC	783585236476

## Dimensions

Dimensions 3.28 in x 2.12 in x 2.36 in

Display Size	Standard Sized Product
Height	2.36 in
Length	3.28 in
Weight	0.75 lb
Width	2.12 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
----------------------	-----------------------------------------------------------------------------------------------------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL3771](#)  
[Warranty - Industrial & Commercial Products](#)