

# Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Hubbell Wiring Device-Kellems  
Catalog # [CS8375](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

## General

Catalog Number	CS8375
Color	Metallic
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single Flanged Inlet
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Blades - Brass</li><li>• Casing - Steel, zinc plated</li><li>• Terminal Retainer - Phenolic</li><li>• Terminal Screws - Steel</li></ul>
Type	Flanged Inlet
UPC	783585829098

## Dimensions

Dimensions 2.17 in x 3.50 in x 2.62 in

Display Size	Standard Sized Product
Height	2.62 in
Length	2.17 in
Weight	0.85 lb
Width	3.5 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3-Phase Delta 250 VAC
Voltage Rating Description	3-Phase Delta 250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
----------------------	-----------------------------------------------------------------------------------------------------------

## Logistics

Carton Quantity	10
Pallet Quantity	810

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS8375](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand