

# Locking Devices, Twist-Lock®, Industrial, Male Plug, 50A 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems  
Catalog # [CS8465C](#)

Twist-Lock® Industrial Male Plug, 50A 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #10 AWG - #6 AWG stranded copper wire only

## General

Catalog Number	CS8465C
Color	Black, White
Cord Range	.830"-1.250"(21.08-31.75)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Insulgrip Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Blade Holder - Polyester</li><li>• Blades - Brass</li><li>• Cord Grip - Polyester</li><li>• Housing - Nylon</li><li>• Shell - Stainless Steel</li><li>• Terminal Screws - Stainless steel</li></ul>
Type	Plugs
UPC	783585829166

## Dimensions

Dimensions	6.37 in x 2.56 in x 2.56 in
Display Size	Standard Sized

Height	2.56 in
Length	6.37 in
Weight	1.25 lb
Width	2.56 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

## Conductor Related

Cable Range	0.830 - 1.250 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	1360

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CS8465C](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-CS8465C-SPEC-EN | REV 10/2024