



Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Plug, 200A 600V AC, 3-Pole 4- Wire Grounding Style 2 , Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL4200PS2W](#)



Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Plug, 200A 600V AC, 3-Pole 4- Wire Grounding Style 2, Terminal Screws, Gray and Black, Watertight

Features

- Locking ring provides UL Type 4X watertight, dust-tight seal
- Catalog number and rating visible while in use
- All-Brass sleeve contacts provide reliable electrical contact

Application

Metallic with Nylon Shroud

General

Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 3,000V AC • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability (Enclosure) - UL 94V-0 and CSA C22.2 No. 0.17 • Environmental - Moisture Resistance - Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94 • Environmental - Operating Temperatures - Max. Continuous 75°C • Min. -40°C w/o impact -25° with impact • Mechanical - Impact Resistance - Per CSA C22.2, No. 182.1, UL 1682

Dimensions

Display Size Standard Sized

Electrical Ratings

Amperage Rating	200 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	200 A
Current Rating	200 A
Voltage Rating	600 VAC/250 VDC
Voltage Rating Description	600V AC/250V DC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#1 AWG to #250MCM

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to CSA Spec. C22.2 No. 159 • UL Listed and CSA Certified Type 4X • UL Standard 1682, UL 50, and UL 1010
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 1

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Product Identification - Identification and ratings are permanently fastened to the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 1686(1, 2, 3, Green)

Series UL 1686 Class 1 Insulgrip®
Style Standard Service, Style 2
Type Watertight Plug
UPC 783585011486



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL4200PS2W-SPEC-EN | REV 1/2024