



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 30A 3-Phase Delta 600 V AC,

By Hubbell Wiring Device-Kellems  
Catalog # [HBL430MIF5W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 30A 3-Phase Delta 600 V AC, 3-Pole 4-Wire Grounding

## Application

High Ampacity Connections

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V AC Min</li> <li>• Electrical - Max Working Voltage - 600V AC</li> <li>• Environmental - Flammability - UL94-5VA and V-0 Classification</li> <li>• Environmental - Ingress Protection - IP66 Suitability</li> <li>• Environmental - Operating Temperatures - Max. Continuous +75°C</li> <li>• Min. Continuous -40°C</li> <li>• Environmental - UV Resistance - All materials are UV stabilized</li> <li>• Mechanical - Impact Resistance - In accordance with UL 746C</li> <li>• Mechanical - Mounting - External adjustment feet</li> <li>• Mechanical - Terminal Identification - In accordance with UL, CSA</li> </ul>

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC
Wattage	18000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed for US and Canada</li> </ul>
Nema Rating	Non-NEMA

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

and international  
conventions

Series	Fused
Style	Standard Service
Type	Mechanical Interlock
UPC	783585405933



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL430MIF5W-SPEC-EN | REV 1/2024