

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 30A 3-Phase Delta 480 V AC,

By Hubbell Wiring Device-Kellems
Catalog # [HBL430MIF7W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female Fused Mechanically Interlocked Receptacle, 30A 3-Phase Delta 480 V AC, 3-Pole 4-Wire Grounding

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max Working Voltage - 600V AC
- Environmental - Flammability - UL94-5VA and V-0 Classification
- Environmental - Ingress Protection - IP66 Suitability
- Environmental - Operating Temperatures - Max. Continuous +75°C
- Min. Continuous -40°C
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustment feet
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBL430MIF7W
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Fused
Specifications	<ul style="list-style-type: none"> • Base and Top - Valox® • Enclosure Gasket - Neoprene • Handle - Valox® • Shaft - Brass



Style
Type
UPC

- Shaft Seal - Neoprene
- Standard Service
- Mechanical Interlock
- 783585405940

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC
Wattage	14400

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed for US and Canada
Nema Rating	Non-NEMA

Logistics

Carton Quantity	1
Pallet Quantity	35

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL430MIF7W](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand