

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
VariLoad, Flush Receptacle, 30A
250V DC/600V AC, 4-Pole 5-Wire
Grounding, Non- NEMA, Screw
Terminal, Unique Center Pin**

By Hubbell Wiring Device-Kellems
Catalog # [HBL45105](#)

Locking Devices, Twist-Lock®, VariLoad®, Flush Receptacle, 30A
250V DC/600V AC, 50-400 Hz 4-Pole 5-Wire Grounding, Non-
NEMA, Screw Terminal, Black, Unique Center Pin.



General

Application	
Catalog Number	HBL45105
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Variload® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17 Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #14 AWG - #10 AWG solid or stranded copper wire only. Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Receptacle Receptacle
UPC	783585236506

Dimensions

Dimensions	3.28 in x 1.72 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	3.28 in
Weight	0.35 lb
Width	1.72 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Listed to UL 498
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL45105-SPEC-EN | REV 6/2024