

# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 480V AC

By Hubbell Wiring Device-Kellems  
Catalog # [HBL460MIF7W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, Terminal



## Application

- High Ampacity Connections

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max Working Voltage - 600V AC
- Environmental - Flammability - UL94-5VA and V-0 Classification
- Environmental - Ingress Protection - IP66 Suitability
- Environmental - Operating Temperatures - Max. Continuous +75°C
- Min. Continuous -40°C
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustment feet
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

## General

Catalog Number	HBL460MIF7W
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Fused
Specifications	<ul style="list-style-type: none"> <li>• Base and Top - Valox®</li> <li>• Enclosure Gasket - Neoprene</li> <li>• Handle - Valox®</li> <li>• Shaft - Brass</li> </ul>

Style	• Shaft Seal - Neoprene
Type	Standard Service
UPC	Mechanical Interlock 783585406022

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC
Wattage	28800

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed for US and Canada</li> </ul>
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	1
Pallet Quantity	35

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL460MIF7W](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand