

HUBBELL
Wiring Device-Kellems

**Locking Devices, Hubbellock,
Industrial, Female Connector Body,
30A 3-Phase Delta 480V AC, 3-Pole
4-Wire Grounding, Non-NEMA,
Screw Terminal, Red**

By Hubbell Wiring Device-Kellems
Catalog # [HBL20444B](#)

Hubbellock® Industrial Female Connector Body, 30A 480V AC,
3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal nylon
housing, thermoset interior



General

Application	
Catalog Number	HBL20444B
Color	
Cord Range	0.70"-1.20" (17.78-30.5)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Grounding Hubbellock® Female Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage Withstand - 2,000V minimum Environmental - Flammability - UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors Environmental - Moisture Resistance - IP30 Suitability Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #10 AWG - #6 AWG stranded copper wire only. Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Connector Body
	Connector Body
UPC	783585017433

Dimensions

Dimensions	6 in x 2.44 in x 2.44 in
Display Size	Standard
Height	2.44 in
Length	6 in
Weight	1.05 lb
Width	2.44 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

Conductor Related

Cable Range	0.700 - 1.200 in
Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Listed to UL 498
----------------------	--

Logistics

Carton Quantity	10
Pallet Quantity	910

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL20444B-SPEC-EN | REV 6/2024