


**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices, Male Plug,  
Insulgrip, Hospital Grade, Straight,  
2-Pole 3-Wire Grounding, 15A 125V,  
5-15P, Transparent, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8215CT](#)

Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade,  
Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Transparent,  
Single Pack.



## General

Application	
Catalog Number	HBL8215CT
Color	Transparent
Cord Range	0.230"-0.720" (5.8-18.3)
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2000V AC minimum
	Environmental - Flammability - UL 94 HB or better
	Environmental - IP Suitability - IP20
	Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #18-10 AWG
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Hospital Grade
Style	Insulgrip
Type	Plug
	Plug
UPC	783585179308

## Dimensions

Dimensions	1.97 in x 1.53 in x 1.53 in
Height	1.53 in
Length	1.97 in
Weight	0.15 lb
Width	1.53 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 42 File 285
	Fed. Spec. W-C-596
	UL Listed to UL498 File No. E2186
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	3600

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Healthcare Product Solutions](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL8215CT-SPEC-EN | REV 6/2024