

# Locking Devices, Hubbellock, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non NEMA, Screw Terminal, Blue

By Hubbell Wiring Device-Kellems  
Catalog # [HBL26519](#)



Locking Devices, Hubbellock®, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding Hubbellock® Plug, Black phenolic interior with Blue thermoplastic sleeve and steel housing, Non NEMA, Screw Terminal

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage Withstand - 2,000V minimum
- Environmental - Flammability - HB or better
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #8 AWG - #4 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL26519
Color	Blue
Cord Range	0.920"-1.450"(23.36-36.83)
EU RoHS Indicator	Contact Manufacturer
Item Type	60A Hubbellock® Plug
Material	Nylon
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Stainless Steel</li><li>• Contacts - Brass</li><li>• Cord Clamp Material - PET</li><li>• Device Color - Black/White</li><li>• Housing - Nylon</li><li>• Plug Housing - Thermoset</li><li>• Terminal Screws - Zinc plated steel</li></ul>
Type	Plugs
UPC	783585017334

## Dimensions

Dimensions	3.03 in x 3.03 in x 5.90 in
Height	5.9 in
Length	3.03 in
Weight	2.1 lb
Width	3.03 in

## Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

## Conductor Related

Cable Range	1.000 - 1.50 in
Number Of Wires	5-Wire
Wire Size	#8 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA Standard</li><li>• Listed to UL Standard</li></ul>
----------------------	---

## Logistics

Carton Quantity	5
Pallet Quantity	770

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL26519](#)  
[Warranty - Industrial & Commercial Products](#)