

Locking Devices, Hubbellock, Industrial, Flanged Inlet, 60A 600V AC, 4-Pole 5-Wire Grounding, Non NEMA, Screw Terminal, Blue

By Hubbell Wiring Device-Kellems
Catalog # [HBL26522](#)

Locking Devices, Hubbellock®, Industrial, Flanged Inlet, 60A
600V AC , 4-Pole 5-Wire Grounding, Black phenolic interior with
steel housing and flange, Non NEMA, Screw Terminal, Blue

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #8 AWG - #4 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26522
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	60A Grounding Hubbellock® Flanged Inlet
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Contacts - Brass• Flanged Housing - Zinc plated steel• Inlet Interior - Phenolic• Terminal - Copper• Terminal Screws - Stainless Steel



Type	Flanged Inlet
UPC	783585017624

Dimensions

Dimensions	3.95 in x 4.12 in x 4.12 in
Display Size	Standard Sized Product
Height	4.12 in
Length	3.95 in
Weight	1.75 lb
Width	4.12 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA Standard• Listed to UL Standard
----------------------	-------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL26522](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand