

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Industrial, Flush Receptacle, 30A 3-  
Phase Wye 277/480V AC, 4-Pole 4-  
Wire Non- Grounding, L19-20R,  
Screw Terminal, Black.**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2760](#)

Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A  
3-Phase Wye 277/480V AC, 4-Pole 4-Wire Non- Grounding, L19-  
20R, Screw Terminal, Black.



## General

Application	
Catalog Number	HBL2760
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	5
Item Type	30A Non-Grounding Single Flush Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
	Environmental - Moisture Resistance - IP20 Suitability
	Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
	Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Single Flush Receptacle
	Single Flush Receptacle
UPC	783585236216

## Dimensions

Dimensions	3.28 in x 1.7 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	3.28 in
Weight	0.3 lb
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 277/480 VAC
Voltage Rating Description	3 Phase WYE 277/480 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42
	Fed.Spec. W-C-596
	Listed to UL 498
Nema Rating	L19-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	2520

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2760-SPEC-EN | REV 6/2024