



Wiring Device-Kellems

# Switches and Motor Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Stainless Steel, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3SS](#)



Switches and Motor Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Stainless Steel, NEMA 4X Enclosure

### Features

- Molded-in conduit opening and field installed hub
- Internal frame automatically bonds all grounds
- Reversible interior accommodates top or bottom conduit opening

### Application

Labelless

### General

Mounting Method	Feet are fixed
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current &amp; voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3000V AC minimum</li> <li>• Electrical - Max. Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94-5VA and V0 Classification</li> <li>• Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact</li> <li>• Environmental - UV Resistance - All materials are UV stabilized</li> <li>• Mechanical - Impact Resistance - In accordance with UL 746C</li> <li>• Mechanical - Mounting - Stainless Steel - Feet are fixed</li> <li>• Mechanical - Product Identification -</li> </ul>

### Dimensions

Dimensions	8.38 in x 4.87 in x 5.39 in
Height	5.39 in
Length	8.38 in
Width	4.87 in

### Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

### Certifications and Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Safety Product Guide](#)
- [Warranty - Industrial & Commercial Products](#)

	Identification and ratings are part of external label
	<ul style="list-style-type: none"><li>• Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions</li></ul>
Series	<ul style="list-style-type: none"><li>• Non-Fused</li><li>• MotorQuick/LINKOSITY</li></ul>
Style	<ul style="list-style-type: none"><li>• Heavy Duty</li><li>• Replacement Switches</li></ul>
Type	<ul style="list-style-type: none"><li>• Disconnect Switches</li><li>• Accessories For LINKOSITY®</li><li>• Disconnect Switches</li><li>• Accessories For LINKOSITY®</li></ul>
UPC	783585242736



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBLDS3SS-SPEC-EN | REV 1/2024