

HUBBELL
Wiring Device-Kellems

**4-PLEX Surge Suppression
Receptacle, 2Pole 3Wire, 15A 125V,
5-15R, Ivory.**

By Hubbell Wiring Device-Kellems
Catalog # [HBL415IS](#)

4-PLEX Surge Suppression Receptacle, 2-Pole 3-Wire, 15A 125V,
5-15R



General

Application	4-Plex with LED
Catalog Number	HBL415IS
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Indicator(s) Type	LED Only
Item Type	Surge Protection Receptacles
Material	Polycarbonate
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Outlet	Straight Blade
Performance	Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V-2
	Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #14-12 AWG stranded or solid copper conductor only
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Response Time	5
Series	4-Outlet Receptacle
UPC	783585017860

Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard
Height	4.3 in
Length	4.3 in
Weight	0.35 lb
Width	0.92 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA 22.2, No. 42 File 285
	Listed to UL Standard 498 File E2186
	NEMA® WD-6 Compliant
Nema Rating	5-15R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL415IS-SPEC-EN | REV 6/2024