



Straight Blade Devices, Receptacles, Panel Mount Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5658](#)



Straight Blade Devices, Receptacles, Panel Mount Single,
Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-
15R, Brown, Single Pack

Features

- Slender/compact design
- Triple wipe contacts
- Panel mount

Application

Extra Heavy Duty

General

Color	Brown
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1.5
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only • Mechanical - Terminal Identification - Terminals
-------------	---

Dimensions

Dimensions	1.75 in x 1.13 in x 1.47 in
Display Size	Standard Sized Product
Height	1.47 in
Length	1.75 in
Weight	0.15 lb
Width	1.13 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Guide RTRT Fed Spec WC596G • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)

identified in accordance
with UL 498 and CSA

Warranty - Industrial & Commercial Products

Series	Extra Heavy Duty
Style	Panel Mount
Type	Single Receptacle
UPC	783585014388



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5658-SPEC-EN | REV 1/2024