

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices,
Receptacles, Duplex, Isolated
Ground, Commercial Grade, 2-Pole
3-Wire Grounding, 20A 125V, 5-
20R, Back and Side Wired**

By Hubbell Wiring Device-Kellems
Catalog # [IG5352I](#)

Straight Blade Duplex Receptacle, Isolated Ground, Commercial
Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Back and
Side Wired



General

Application	
Catalog Number	IG5352I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact °C
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94 V-2 Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Hubbell-PRO
Style	Smooth Face
Type	Isolated Ground Isolated Ground
UPC	783585146812

Dimensions

Dimensions	3.28 in x 1.57 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in
Weight	0.15 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA 22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-IG5352I-SPEC-EN | REV 6/2024