

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 30A 4-Wire

By Hubbell Wiring Device-Kellems
Catalog # [IN430DF](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 30A 4-Wire, Furnished with Screws, Black Thermoset Polyester

Application

High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max Working Voltage - 600V AC RM
- Environmental - Flammability - UL94-5VA and V-0 classification
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Operating Temperatures - Max. Continuous:75°C
- Min. Continuous:-40°C w/o impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

General

Catalog Number	IN430DF
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Watertight When Installed
Item Type	Replacement Interior
Material	Thermoset
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Accessories
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless Steel• Contact Carrier - High-Impact Thermoset

- Gaskets - Neoprene
- Hinge Spring - Stainless Steel
- Terminal Screws - Stainless Steel

Style	For Receptacles/Connectors
Type	Replacement Interior
UPC	783585420240

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
Pallet Quantity	2560

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - IN430DF](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand