



Wiring Device-Kellems

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 4-Pole 4-Wire Non- Grounding, 60A 3 Phase 120/208 V AC, 18-60R



By Hubbell Wiring Device-Kellems
Catalog # [HBL7303C](#)

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 4-Pole 4-Wire Non-Grounding, 60A 3 Phase 120/208 V AC, 18-60R, Black, Single Pack.

Features

- Catalog number, ratings and certifications molded in face
- Gripping ribs provide secure gripping area
- Supertough nylon housing

General

Color	<ul style="list-style-type: none"> • Black • Noir
Cord Range	0.625"-1.310"
Horsepower - Maximum	7.5
Material	Nylon
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only • Mechanical - Terminal Identification - Terminals

Dimensions

Dimensions	4.13 in x 2.88 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.85 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed File E1706
Nema Rating	18-60P

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

identified in accordance
with UL 498 and CSA

Series	Extra Heavy Duty
Style	Non-Grounding
Type	<ul style="list-style-type: none">• Plug• Plugs
UPC	783585015385



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL7303C-SPEC-EN | REV 1/2024