

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Male Plug,
Heavy Duty,
Industrial/CommercialGrade,
Straight, 3-Pole 3-Wire Non
Grounding, 50A 125/250V, 10-50P,
Single Pack**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7513C](#)

Straight Blade Devices, Male Plug, Heavy Duty,
Industrial/CommercialGrade, Straight, 3-Pole 3-Wire Non
Grounding, 50A 125/250V, 10-50P , Black, Single Pack.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL7513C
Color	Black
Cord Range	0.625"-1.218"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	3
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">Blade Holder - Reinforced Thermoplastic PolyesterBlades - BrassBox Terminals - Copper AlloyCord Clamps - Reinforced Thermoplastic PolyesterHousing - Supertough Nylon
Style	Non-Grounding
Type	Plug

UPC

783585015101

Dimensions

Dimensions	4.13 in x 2.88 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.8 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA CertifiedUL Listed File E1706
Nema Rating	10-50P

Logistics

Carton Quantity	5
Pallet Quantity	720

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7513C](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL7513C-SPEC-EN | REV 10/2024