

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices, Male Plug,  
Valise Series, Hospital Grade,  
Straight, 2-Pole 3-Wire Grounding,  
15A 125V, 5- 15P, White, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8115V](#)

Straight Blade Devices, Male Plug, Valise Series, Hospital Grade,  
Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15P, White,  
Single Pack.



## Application

- Hospital Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2000V AC minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #16 to #12 AWG
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL8115V
Color	<ul style="list-style-type: none"><li>White</li><li></li></ul>
Cord Range	0.300"-0.660" (7.6-16.8)
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Valise Plug
Material	Nylon
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hospital Grade
Style	Valise
Type	<ul style="list-style-type: none"><li>Plugs</li><li>Plugs</li></ul>
UPC	783585015637

## Dimensions

Dimensions	1.88 in x 1.25 in x 1.13 in
Height	1.13 in
Length	1.88 in
Weight	0.15 lb
Width	1.25 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #12 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>Certified to CSA, C22.2, No. 42 File 285</li><li>Fed. Spec. W-C-596</li><li>NEMA® WD-6 Compliant</li><li>UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	6000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Healthcare Product Solutions](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL8115V-SPEC-EN | REV 7/2024