

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Male Plug,
Nylon, Heavy Duty,
Industrial/Commercial Grade,
Angled, 2-Pole 3-Wire Grounding,
30A 125V, 5-30P, Single Pack.**

By Hubbell Wiring Device-Kellems
Catalog # [HBL9309](#)

Straight Blade Devices, Male Plug, Nylon, Heavy Duty,
Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding,
30A 125V, 5-30P, Black, Single Pack.



Features

- Nylon
- Heavy Duty
- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#4 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9309
Color	Black
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Blade Holder - Reinforced Thermoplastic Polyester• Box Terminals - Brass• Cord Clamp - Reinforced Thermoplastic Polyester• Housing - Supertough Nylon• Terminal Retainer - Reinforced Thermoplastic

Style	Polyester
Type	Grounding
UPC	Plug 783585015224

Dimensions

Dimensions	4.34 in x 2.75 in x 1.88 in
Height	1.88 in
Length	4.34 in
Weight	0.55 lb
Width	2.75 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Nema Rating	5-30P
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	1360

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL9309](#)
[Warranty - Industrial & Commercial Products](#)

