

Straight Blade Devices, Male Plug, Nylon, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 4-Wire Grounding, 60A 125/250V, 14-60P.



By Hubbell Wiring Device-Kellems
Catalog # [HBL9461C](#)

Straight Blade Devices, Male Plug, Nylon, Heavy Duty,
Industrial/Commercial Grade, Straight, 3-Pole 4-Wire Grounding,
60A 125/250V, 14-60P, Black, Single Pack.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9461C
Color	Black
Cord Range	0.625"-1.310"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	3
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Blade Holder - Reinforced Thermoplastic Polyester• Blades - Brass• Box Terminals - Copper Alloy• Housing - Supertough Nylon• Mounting Screw - Stainless steel
Style	Grounding
Type	Plug

UPC 783585015354

Dimensions

Dimensions	4.13 in x 2.88 in x 2.88 in
Height	2.88 in
Length	4.13 in
Weight	0.8 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	<ul style="list-style-type: none">• 125/250 V• 125 V V V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed File E1706
Nema Rating	14-60P

Logistics

Carton Quantity	5
Pallet Quantity	680

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL9461C](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL9461C-SPEC-EN | REV 10/2024