



# Heavy Duty Products, Switched Twist-Lock®, Industrial Grade, Accessories, Mechanical Interlock, 30A 600V AC, Single Conductor, Terminal Screws, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [HBLMITL](#)



Heavy Duty Products, Switched Twist-Lock®, Industrial Grade, Accessories, Mechanical Interlock, 30A 600V AC, Single Conductor, Terminal Screws, Gray

## Features

- Unfused Mechanical Interlock for Watertight Safety-Shroud
- Virtually Eliminates Possible Circuit Making or Breaking While Under Load
- Compact, Corrosion Resistant Type 4X Non-metallic Enclosure
- Molded Valox Resists Abuse, Corrosion and Enhances Safety

## General

Color	Gray
Item Type	Safety-Shroud Enclosure
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V minimum</li> <li>• Electrical - Max. Working Voltage - 600V RMS</li> <li>• Electrical - Operations - Mechanical 10,000 cycles</li> <li>• Electrical 6,000 cycles</li> <li>• Environmental - Flammability - Meets UL 94V0 material classification</li> <li>• Environmental - Moisture Resistance - IP66 suitability</li> <li>• Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C</li> <li>• Environmental - UV Resistance - All exposed materials are UV stabilized</li> <li>• Mechanical - Impact Resistance - In accordance with UL 746C</li> <li>• Mechanical - Mounting -</li> </ul>

## Dimensions

Dimensions	11.44 in x 4.88 in x 4.19 in
Height	4.19 in
Length	11.44 in
Weight	3.65 lb
Width	4.88 in

## Electrical Ratings

Dielectric Strength	Withstands 3,000V minimum
---------------------	---------------------------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating</li> <li>• Listed to UL Standard</li> </ul>
Nema Rating	Type 4X

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

External full adjustable feet

- Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA

Style

For 20A and 30A Devices

Type

- Switched Enclosure
- Switched Enclosure

UPC

783585176802



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBLMITL-SPEC-EN | REV 1/2024