

HUBBELL
Wiring Device-Kellems

**Heavy Duty Products, Single Pole
Devices, Industrial Grade, Male,
Receptacle, 300/400A 600V
AC/DC, Single Conductor, Set
Screw, Blue**

By Hubbell Wiring Device-Kellems
Catalog # [HBLMRBL](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male,
Receptacle, 300/400A 600V AC/DC, Single Conductor, Set
Screw, Blue



Features

- Industrial Grade
- Male
- Receptacle

Application

High Ampacity Connections

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #4 to 4/0 AWG

General

Catalog Number	HBLMRBL
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Flanged Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 16
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer• Contact Material - Brass• Mounting Hole - 4x #10-32• Retaining Screw Material - Nylon• Termination - (2) 7/32 Socket Head Set Screws

Style	Double Set Screw Male
Type	Receptacle
UPC	783585112947

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	400 A
Connectivity	Screw Terminals
Current / Amperage Rating	400 A
Current Rating	400 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	240000

Conductor Related

Wire Size	#4 AWG to #4/0 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	1575

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Single Pole Devices](#)
[Specifications - HBLMRBL](#)
[Warranty - Industrial & Commercial Products](#)

